

Product data sheet

Specifications

Fibre patch panel, Actassi, 1U, 48-fibre, LC duplex, unloaded



ACTFM1UBLC48U

Main

Range Of Product	Actassi
Product Or Component Type	Fibre patch panel
Device Application	Telecom
Device Presentation	Empty
Provided Equipment	1 Pg 9 cable gland
Colour	Dark grey (RAL 7016)

Complementary

Product Compatibility	24 LC duplex adaptor
Number Of Optic Fibre	48
Number Of Rack Unit	1U
Type Of Installation	Indoor
Mounting Support	19" rack
Height	43 mm
Width	480 mm
Depth	260 mm
Targeted Region	Europe Asia Pacific.

Environment

Ambient Air Temperature For Operation	20...60 °C
Ambient Air Temperature For Storage	20...60 °C
Standards	EIA-310D

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	30.5 cm
Package 1 Length	53.0 cm
Package 1 Weight	2.705 kg
Unit Type Of Package 2	S04

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	4
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	11.692 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations