

# Product data sheet

Specifications

## Actassi Indoor Fibre Cable Tight Buffered OS2 9/125µm 4-Core LSZH



ACTND04SM9LS

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

Range	Actassi
Product	Fibre optic cable single mode
Device Application	Communication
Cable Packaging	Reel

### Complementary

Maximum Attenuation	0.3 dB / 1 km at 1550 nm 0.45 dB / 1 km at 1310 nm
Fibre Performance	OS2 9/125 µm
Optic Fibre Type	Tight buffered diameter: 900 µm
Number Of Optic Fibre	4
Bending Radius	10 x overall diameter long term 20 x overall diameter short term
Pulling Force	660 N installed 200 N operation
Crush Resistance	10000 N/m
Colour	Sheath: yellow
Type Of Installation	Indoor
Diameter	4.8 mm cable +/- 0.2 mm
Cable Weight	21.6 kg / 1 km
Targeted Region	Asia Pacific.

### Environment

Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-20...60 °C
Flame Retardance	LSZH
Environmental Characteristic	Strength: aramid yarn Flame retardant:
Standard	conforming to IEC 60332-3C conforming to IEC 754-3 conforming to NES 713 conforming to IEC 1034

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	6 cm
Package 1 Length	5.5 cm
Package 1 Weight	29.6 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations