

Product data sheet

Specifications



Patch cord, Actassi, Category 6A, S/FTP, LSZH, 3 m, white

ACTPC6ASFLS30WE

Main

Range	Actassi
Product	Patch cord
Device Application	Communication
Colour	White
Cable Shielding Type	S/FTP

Complementary

Type Of Cable	4 pair cables
Length (Customizable Value In Configurator)	3 m
Communication Network Category	6 _A
Transmission Frequency	500 MHz
Contacts Material	Phosphor bronze with 50 micro-inches gold over 100 micro-inches nickel
Awg Gauge	AWG 28
Maximum Number Of Cord Per Bundle	48 in cabinet for 4PPoE Type 3 (up to 60 W) 24 in cabinet for 4PPoE Type 4 (up to 90 W)
Maximum Patch Cord Cumulated Length	10 m with 84 m 2-point permanent link at 20 °C 7 m with 90 m 2-point permanent link at 20 °C
Minimum Number Of Matings	750 cycles
Cable Outer Diameter	5.5 mm +/- 0.2 mm
Material	Copper: conductor PE (polyethylene): wire insulation Aluminium/polyester: foil Tin plated copper: braid shield PE (polyethylene): sheath

Environment

Flame Retardance	LSZH
Standards	ISO/IEC 11081-2017 performance TIA/EIA-568-C.2 performance EN 50173-2018 performance IEC 61935-2 performance

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	14.000 cm
Package 1 Length	21.000 cm
Package 1 Weight	119 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	38
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.250 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations