

Product data sheet

Specifications



Patch cord, Actassi, Category 6A, S/FTP, LSZH, 3 m, white

ACTPC6ASFLS30WE

Main

Range	Actassi
Product	Patch cord
Device application	Communication
Colour	White
Cable shielding type	S/FTP

Complementary

Type of cable	4 pair cables
Length (customizable value in configurator)	3 m
Communication network category	6A
Transmission frequency	500 MHz
Contacts material	Phosphor bronze with 50 micro-inches gold over 100 micro-inches nickel
AWG gauge	AWG 28
Maximum number of cord per bundle	48 in cabinet for 4PPoE Type 3 (up to 60 W) 24 in cabinet for 4PPoE Type 4 (up to 90 W)
Maximum patch cord cumulated length	10 m with 84 m 2-point permanent link at 20 °C 7 m with 90 m 2-point permanent link at 20 °C
Minimum number of matings	750 cycles
Cable outer diameter	5.5 mm +/- 0.2 mm
Material	Copper: conductor PE (polyethylene): wire insulation Aluminium/polyester: foil Tin plated copper: braid shield PE (polyethylene): sheath

Environment

Flame retardance	LSZH
Standards	ISO/IEC 11081-2017 performance TIA/EIA-568-C.2 performance EN 50173-2018 performance IEC 61935-2 performance

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	14.000 cm
Package 1 Length	21.000 cm
Package 1 Weight	119 g
Unit Type of Package 2	S03
Number of Units in Package 2	38
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.250 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes

Recommended replacement(s)