

# Product data sheet

Specifications

## Cable duct - 90 x 30 mm - without cover - blue



AK2GA39

### Main

Product Or Component Type	Cable duct
Accessory / Separate Part Category	Cabling accessories
Range Compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity Per Set	Set of 8

### Complementary

Colour	Blue (RAL 5000)
Fixing Mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	90 mm
Length	2000 mm
Width	30 mm
Net Weight	1.12 kg
Total Number Of Wires	200

### Environment

Ambient Air Temperature For Operation	-5...60 °C
Flame Retardance	V-0 conforming to UL 94
Fire Resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 NF C 68-102 VDE 0660

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	8.5 cm
Package 1 Length	200.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1.675 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	8
Package 2 Height	8.5 cm
Package 2 Width	18.5 cm
Package 2 Length	200.0 cm
Package 2 Weight	13.4 kg
Unit Type Of Package 3	P2M
Number Of Units In Package 3	336
Package 3 Height	120 cm
Package 3 Width	202 cm
Package 3 Length	70 cm
Package 3 Weight	235 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)