

Product data sheet

Specifications



Mounting plate, Linergy HK, 1P+N, 4.4mm², 190x54x61mm

AK5PA212N3

Main

Range	Linergy
Product Name	HK
Product Or Component Type	Mounting plate
Poles Description	1P + N
[Ith] Conventional Free Air Thermal Current	25 A
I ² T On Activation	200000 A ² .s
Number Of Cables	2 cable(s) 4 mm ² at 105 °C
Width	54 mm
Height	190 mm
Depth	61 mm

Complementary

[Ui] Rated Insulation Voltage	690 V conforming to IEC 60439-1
Electrical Connection	Connector
9 Mm Pitches	6
Net Weight	0.23 kg

Environment

Standards	IEC 60439
Product Certifications	LROS (Lloyds register of shipping) DNV CSA UL

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	7.5 cm
Package 1 Length	22.0 cm
Package 1 Weight	361.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	10

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.046 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)