


Product data sheet

Specifications



2 POLE DOUBL PLAT PH1 PH2

AK5PA212PH12

 **Discontinued on:** Jun 27, 2020

 **Discontinued**

Main

Range	Linergy
Product Name	HK
Product Or Component Type	Mounting plate
Poles Description	2P
[Ith] Conventional Free Air Thermal Current	25 A
I²T On Activation	200000 A².s
Number Of Cables	2 cable(s) 4 mm² at 105 °C
Width	54 mm
Height	190 mm
Depth	61 mm

Complementary

[Ui] Rated Insulation Voltage	690 V conforming to IEC 60439-1
9 Mm Pitches	6
Net Weight	0.23 kg

Environment

Standards	IEC 60439
Product Certifications	UL CSA LROS (Lloyds register of shipping) DNV

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	8 cm
Package 1 Length	22.5 cm
Package 1 Weight	359 g

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months