

# Product data sheet

Specifications



## Multifix Plus - apparatus box - 3 gangs - without cover - 67x40mm

ALB71337

### Main

Range Of Product	Multifix
Range	Multifix
Product Name	Multifix Plus
Product Or Component Type	Apparatus box
Device Presentation	Without cover
Quantity Per Set	Set of 10

### Complementary

Function Available	Anti-rotation system
Number Of Gangs	3 gangs
Installation Direction	Vertical
Fixing Mode	By screws and claws
Material	PS (polystyrene)
Mechanical Robustness	Fire resistance
Colour Tint	Box: blue (RAL 5015)
Cable Entry	6 knock-out
Distance Between Centers	57 mm
Height	185 mm
Width	71 mm
Depth	40 mm
Connections - Terminals	Screwed
Diameter	67 mm
Distance Between Supports	60 mm
Tube Diameter	0.84 mm
Internal Depth	38 mm
Length	215 mm
Maximum Cable Cross Section	2.5 mm²
Sealing	Without
Surface Treatment	Untreated

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP20
Standards	IEC 60670-1

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	7.0 cm
Package 1 Length	19.0 cm
Package 1 Weight	62.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	11.8 cm
Package 2 Width	20.0 cm
Package 2 Length	33.5 cm
Package 2 Weight	742.0 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	50
Package 3 Height	30.0 cm
Package 3 Width	40.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	4.589 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations