


Product data sheet

Specifications



MasterSwitch Pwr Recept, 2U, 15A, 120V, (2)5-15

AP9510515

 **Discontinued on:** Jun 14, 2022

 **Discontinued**

Overview

Lead Time While Supplies Last

Main

Colour Beige

Cable Length 3.05 m

Number Of Cables 1

Provided Equipment User manual

Complementary

Main Input Voltage 120 V

Height 8.38 cm

Width 13.97 cm

Main Output Voltage 120 V

Depth 12.95 cm

Net Weight 1.82 kg

Mounting Location Front
Rear

Mounting Preference No preference

Input Connection Type NEMA 5-15P

Mounting Mode Rack-mounted with kit

Number Of Rack Unit 2U

Mounting Position Horizontal

Permissible Voltage 90...132 V

Max Line Current 15 A

Input Current Limits 15 A

Load Capacity 1800 VA

Number Of Power Socket Outlets 0

Network Frequency 50/60 Hz

Number Of Power Socket Outlets 2 NEMA 5-15R

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	CSA UL listed
Standards	CSA 22.2 No. 950 UL 1950
Ambient Air Temperature For Operation	0...45 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15...65 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...9144.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33.02 cm
Package 1 Width	13.97 cm
Package 1 Length	17.78 cm
Package 1 Weight	2.175 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------