

Product data sheet

Specifications



NetShelter 4 Post Open Frame Rack 44U #12-24 Threaded Holes

AR204A

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Number Of Rack Unit	44U
Provided Equipment	Installation guide

Physical

Colour	Black
Height	213 cm
Width	60 cm
Depth	74.7 cm
Net Weight	41.82 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	73.99 cm
Minimum Mounting Depth	73.99 cm
Rack Width	19"
Permanent Permissible Load	907.18 kg static

Conformance

Standards	EIA-310E
-----------	----------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	208.3 cm
Package 1 Width	18.8 cm
Package 1 Length	25.4 cm
Package 1 Weight	46.36 kg

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH

Resource performance

✔ Take-Back Program Available

Well-being performance

✔ Reach Free Of Svhc

✔ Toxic Heavy Metal Free

✔ Mercury Free

✔ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

Environmental Disclosure [Product Environmental Profile](#)