

Product data sheet

Specifications



NetShelter SV 42U 600mm Wide x 1060mm Deep Enclosure with Sides Black

AR2400

Overview

Presentation	Universal IT enclosure for low to medium density server and networking applications. Compact width to optimize data center space. 42U height to easily roll through doorways.
Lead Time	Usually in Stock

Main

Number Of Rack Unit	42U
Provided Equipment	Baying hardware Doors Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters 4 x bolt down brackets Roof Side panels Unpacking sheet

Physical

Height	205.7 cm
Width	60 cm
Depth	106 cm
Net Weight	112.2 kg
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	77.72 cm
Minimum Mounting Depth	16.76 cm
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent Permissible Load	459.94 kg dynamic 1000.17 kg static

Conformance

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	218.1 cm
Package 1 Width	116 cm
Package 1 Length	74 cm
Package 1 Weight	131.5 kg

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Take-back Transparency RoHS/REACH

Resource performance

✔ Take-Back Program Available

Well-being performance

✔ Reach Free Of Svhc

✔ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile