

# Product data sheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 48U, Black, 2258H x 750W x 1200D mm

AR3357

### Overview

Lead time Usually in Stock

### Main

Number of rack unit 48U

Provided equipment Baying hardware  
Key(s)  
Leveling feet  
Mounting hardware  
Pre-installed casters  
Side panels

### Physical

Height 225.8 cm

Width 75 cm

Depth 120 cm

Net weight 185.45 kg

Colour Black

Mounting preference No preference

Mounting mode Not rack-mountable

Maximum mounting depth 104.8 cm

Minimum mounting depth 26.19 cm

Rack width 19"

Marking 14 gauge EIA mounting rail  
16 gauge front door  
16 gauge post  
16 gauge rear door  
18 gauge roof  
18 gauge side panels

Permanent permissible load 1020.58 kg dynamic  
1700.97 kg static

### Conformance

Standards UL 2416  
UL 60950-1  
EIA-310E

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	240 cm
Package 1 Width	85.1 cm
Package 1 Length	133.4 cm
Package 1 Weight	201.82 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

## Recommended replacement(s)