

Product data sheet

Specifications



125HP460VATV61w/ BacNetandConduitBox

ATV61HD90N4T1BN

 **Discontinued on:** Dec 13, 2023

 **Discontinued**

Main

Asynchronous Motor Control Profile	Variable torque standard
Device Short Name	ATV61
Range Of Product	Altivar 61

Complementary

[In] Rated Current	179 A
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	Modbus BACnet CANopen
Impregnation Material	Conformal coated
Input Voltage	400/480 V AC
Keypad Type	LCD keypad
Motor Power Hp	125 hp
Motor Power Kw	90 kW
Network Number Of Phases	3 phases output 1 phase input

Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	128.82 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications