

Product data sheet

Specifications



2HP 460VATV61 w/ lonworksandconduitbox

ATV61HU15N4T1LW

⚠ Discontinued on: Dec 31, 2017

⚠ End-of-service on: Oct 11, 2022

⚠ Discontinued

Main

Asynchronous Motor Control Profile	Variable torque standard
Device Short Name	ATV61
Range Of Product	Altivar 61

Complementary

[In] Rated Current	4.1 A
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	CANopen LonWorks Modbus
Input Voltage	400/480 V AC
Keypad Type	LCD keypad
Motor Power Hp	2 hp
Motor Power Kw	1.5 kW
Network Number Of Phases	3 phases output 1 phase input
Output Voltage	<= rated supply voltage

Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	6.35 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications