

Product data sheet

Specifications



APC Back-UPS Pro 1050VA, 120V

BP1050

⚠ Discontinued on: Jun 10, 2022

⚠ Discontinued

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	120 V
Rated Power In W	670 W
Rated Power In Va	1050 VA
Output Connection Type	6 NEMA 5-15R
Cable Length	1.83 m
Number Of Cables	1

Batteries & Runtime

Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Extended Runtime	0
Replacement Battery	RBC6

General

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Height	21.6 cm
Width	17 cm
Depth	43.9 cm
Net Weight	19.36 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Input

Network Frequency	50/60 Hz
-------------------	----------

Output

Maximum Configurable Power In W	670 W
Ups Type	Line interactive
Maximum Configurable Power In Va	1050 VA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.6 cm
Package 1 Width	17 cm
Package 1 Length	43.9 cm
Package 1 Weight	21.365 kg
Scc14	00731304221388

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------