

Product data sheet

Specifications



SE Easy UPS, 1000VA, Floor/Wall Mount, 230V, 4x CEE 7/3 Schuko outlets, AVR

BVS1000I-GR

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Product Or Component Type	Uninterruptible power supply (UPS)
Battery Type	Lead-acid battery
Topology	Line interactive
Quantity Per Set	Set of 1
Reset	Automatic reset
Range Of Product	Easy UPS 1Ph BVS Series

Complementary

Type Of Installation	Indoor
Surge Energy	156 J
Type Of Signal	Stepped approximation to a sinewave
Protection Device Type	Surge protection device (SPD) Miniature circuit breaker (MCB) Fuse
Input Voltage	230 V AC
Output Voltage	230 V
Ip Degree Of Protection	IP20
Transfer Time	6 ms typical : 10 ms maximum
Network Frequency	45...65 Hz
Power Range	1000 VA 600 W
Electrical Connection	Input: 1 inlet Schuko CEE 7/P Output: 4 outlet Schuko CEE 7
Local Signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LED for battery status
Number Of Batteries	1
Charging Time	8 h
Battery Voltage	12 V
Battery Capacity	9.0 Ah
Battery Life	5 year(s)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	5.7 kg
Height	92.5 mm
Width	160.5 mm
Depth	305 mm

Environment

Relative Humidity	0...90 %, non-condensing
Operating Altitude	0...6561 ft
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Product Certifications	CE

Physical

Mounting Support	Wall Floor
------------------	---------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.200 cm
Package 1 Width	16.500 cm
Package 1 Length	30.500 cm
Package 1 Weight	5.702 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	23.458 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	32
Package 3 Height	90.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	199.664 kg
Scc14	10731304338403

Contractual warranty

Warranty	2 years
----------	---------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information