

# Product data sheet

Specifications



## SE Easy UPS, 500VA, Floor/Wall Mount, 230V, 4x AS3112 Australian outlets, AVR

BVS500I-AZ

### Overview

Lead Time	Usually in Stock
-----------	------------------

### Main

Product Or Component Type	Uninterruptible power supply (UPS)
Cable Length	1.52 m
Battery Type	Lead-acid battery Sealed rechargeable Internal battery
Range Of Product	Easy UPS 1Ph BVS Series

### Complementary

Display Type	LED indicator
Type Of Signal	Sine wave
Transfer Time	6 ms typical : 10 ms maximum
Network Frequency	50...60 Hz
Power Range	500 VA
Electrical Connection	Output: 4 outlet Australian Input: 1 cable
Local Signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LCD display for status and alert
Charging Time	8 h
Net Weight	3.9 kg
Height	9.25 cm
Width	16.05 cm
Depth	30.5 cm

### Environment

Relative Humidity	0...90 %, non-condensing
Operating Altitude	0...1968.3 m
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Product Certifications	CE RCM

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Physical

Mounting Support	Wall-mount
------------------	------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.362 cm
Package 1 Width	1.422 cm
Package 1 Length	3.734 cm
Package 1 Weight	4.2 kg
Scc14	10731304346453

## Contractual warranty

Warranty	2 years
----------	---------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>