

# Product data sheet

Specifications



## ARGUS Presence HF High Bay - 2ch

CCT551023

### Main

Range Of Product	ARGUS standard movement detector
Range	ARGUS
Product Or Component Type	Presence detector
Load Type	LED lighting: : 100 W Incandescent lamps: : 2000 W - 230 V Halogen lamp: : 1000 W - 230 V Fluorescent tube: 900 VA Compact fluorescent lamp: : 100 W Motor: : 100 W Relay: : 5 A - 250 V Halogen lamp with standard electronic transformer: 1000 VA Halogen lamp with standard ferromagnetic transformer: 1000 VA
Colour Tint	White

### Complementary

Network Frequency	50/60 Hz
Input Function	Switch
Output Voltage	220...250 V
Output Current	10 A
Number Of Channels	2
Control Type	Movement sensor
Function Available	Switching, toggling, dimming
Light Intensity Adjustment	10...2000 lux
Horizontal Detection Angle	360 °
Detection Range	Radius: 7000 mm
Technology Type	High frequency
Mounting Height	2.5 m

### Environment

Ip Degree Of Protection	IP40 IP52
-------------------------	--------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	13 cm
Package 1 Length	16.2 cm
Package 1 Weight	498 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.492 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	144
Package 3 Height	104 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	97 kg

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>