

Product data sheet

Specifications



ARGUS standard indoor, false ceiling 360° - blister

CCTR1P001

Main

Range Of Product	ARGUS standard movement detector
Range	ARGUS
Product Or Component Type	Movement detector
Load Type	Incandescent lamp: 1000 W, AC Halogen lamp: 1000 W, AC Low voltage halogen lamp with wire-wound transformer: 500 VA Low voltage halogen lamp with electronic transformer: 250 VA Fluorescent tube: 200 VA, AC Compact fluorescent lamp: 3 x 23 W, AC Capacitive: : 6 A, 21 µF, AC Capacitive: : 10 A, 14 µF, AC
Colour Tint	White
Type Of Packing	Blister

Complementary

[Ue] Rated Operational Voltage	220...240 V
Network Frequency	50 Hz
[Ue] Rated Operational Voltage	220...240 V
Number Output Current	10 A
Type Of Setting	Light sensitivity adjustable Time adjustment
Time Delay	5 s...10 min
Light Intensity Adjustment	5...2000 lux
Horizontal Detection Angle	0...360 °
Detection Range	Radius: 3.9 m
Material	ABS + PC matt
Device Mounting	Ceiling
Mounting Height	3 m

Environment

Condition Of Use	Indoor use only
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	11 cm
Package 1 Width	18 cm
Package 1 Length	20 cm
Package 1 Weight	300 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	19.2 cm
Package 2 Width	25.6 cm
Package 2 Length	38.6 cm
Package 2 Weight	2.362 kg
Unit Type Of Package 3	S04
Number Of Units In Package 3	18
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	5.59 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information