

# Product data sheet

Specifications



## Stago - t-piece vertical flat 60x120mm pre-galvanized RAL1013

CSU36211212

⚠ Discontinued on: Sep 30, 2020

⚠ End-of-service on: Oct 26, 2020

⚠ Discontinued

### Main

Product Or Component Type	T-piece
---------------------------	---------

### Complementary

Operating Angle	90 °
Direction Change Type	Vertical
Adjustment	Foldable
Product Destination	Cable tray KG281 H= 60 mm W= 120 mm
Fixing Mode	Screwless
Material	Steel pre-galvanized, RAL 1013
Inner Radius	100 mm
Height	27 mm
Width	285 mm
Depth	287 mm

### Environment

Atmospheric-Corrosivity Category	C2
Environmental Characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications