

Product data sheet

Specifications



Stago - t-piece vertical flat 60x330mm pre-galvanized RAL1013

CSU36213312

⚠ Discontinued on: Sep 30, 2020

⚠ End-of-service on: Oct 26, 2020

⚠ Discontinued

Main

Product Or Component Type	T-piece
---------------------------	---------

Complementary

Operating Angle	90 °
Direction Change Type	Vertical
Adjustment	Foldable
Product Destination	Cable tray KG281 H= 60 mm W= 330 mm
Fixing Mode	Screwless
Material	Steel pre-galvanized, RAL 1013
Inner Radius	100 mm
Height	27 mm
Width	434 mm
Depth	436 mm

Environment

Atmospheric-Corrosivity Category	C2
Environmental Characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations