

Product data sheet

Specifications



Stago - horizontal bend 90° H1560 - 60x600 mm - steel - hot-dip galvanized

CSU733223

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Stago
Product Or Component Type	Bend
Cable Support Type	High side
Mounting Location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants

Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Product Destination	Cable ladder WHS H= 60 mm W= 600 mm
Type Of Rung	C-profile
Fixation Rung	Welded
Fixing Mode	By screw
Material With Surface Treatment	Steel hot-dip galvanized
Corrosion Class	C3/C4
Perforation Location	Side perforation
Height	60 mm
Width	600 mm
Net Weight	3 kg / set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications