

# Product data sheet

Specifications



Stago - whs cable ladder  
100x800mm RD=250 L=3m 1.5mm  
hot-dip galvanized

CSU737023

⚠ Discontinued on: Dec 19, 2016

⚠ End-of-service on: Feb 2, 2017

⚠ Discontinued

## Main

Range Of Product	Stago
Product Or Component Type	Cable ladder
Device Short Name	WHS
Cable Support Type	High side
Mounting Location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants

## Complementary

Type Of Rung	C-profile
Fixation Rung	Welded
Rung Dual Spacing	250 mm
Fixing Mode	By screw
Material With Surface Treatment	Steel hot-dip galvanized
Corrosion Class	C3/C4
Thickness	1.5 mm
Perforation Location	Side perforation
Height	100 mm
Width	800 mm
Length	3000 mm
Net Weight	5.433 kg / 100 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications