

# Product data sheet

Specifications



## Stago - horizontal bend 90° H15100 - 100x800 mm - steel - hot-dip galvanized

CSU737037

⚠ Discontinued on: Sep 19, 2018

⚠ Discontinued

### Main

|                           |   |
|---------------------------|---|
| Range Of Product          | Stago   |
| Product Or Component Type | Bend  |
| Cable Support Type        | High side   |
| Mounting Location         | Area with high level of environmental corrosion, humidity and airborne pollution<br>industrial and coastal areas, chemical plants |

### Complementary

|                                 |                                      |
|---------------------------------|--------------------------------------|
| Operating Angle                 | 90 °                                 |
| Direction Change Type           | Horizontal                           |
| Product Destination             | Cable ladder WHS H= 100 mm W= 800 mm |
| Type Of Rung                    | C-profile                            |
| Fixation Rung                   | Welded                               |
| Fixing Mode                     | By screw                             |
| Material With Surface Treatment | Steel hot-dip galvanized             |
| Corrosion Class                 | C3/C4                                |
| Perforation Location            | Side perforation                     |
| Height                          | 100 mm                               |
| Width                           | 800 mm                               |
| Net Weight                      | 8.2 kg / set of 1                    |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications