

Product data sheet

Specifications



Stago - cross piece H17 - 100x300 mm - steel - hot-dip galvanized

CSU737061

 **Discontinued on:** Sep 27, 2019

 **Discontinued**

Main

Range Of Product	Stago
Product Or Component Type	X-junction
Cable Support Type	High side
Mounting Location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants

Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Product Destination	Cable ladder LB4000 H= 100 mm W= 300 mm Cable ladder WHS H= 100 mm W= 300 mm
Type Of Rung	C-profile
Fixation Rung	Welded
Mounting Mode	Push-in
Fixing Mode	By joint screwless Screws
Material With Surface Treatment	Steel hot-dip galvanized
Corrosion Class	C3/C4
Perforation Location	Side perforation
Height	100 mm
Width	1400 mm
Depth	1400 mm
Net Weight	8.91 kg / set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications