

Product data sheet

Specifications



Stago - whs cable ladder 60x600mm RD=200 L=3m 1mm pre-galvanized

CSU737775

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Stago
Product Or Component Type	Cable ladder
Device Short Name	LB4000
Cable Support Type	High side
Mounting Location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Type Of Side Joist	Open profile
Type Of Rung	Perforated profile
Fixation Rung	Welded
Rung Dual Spacing	200 mm
Fixing Mode	By screw
Material With Surface Treatment	Steel pre-galvanized
Corrosion Class	C2
Thickness	1 mm
Perforation Location	Side perforation
Height	60 mm
Width	600 mm
Length	3 m
Net Weight	3.145 kg / 100 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11 cm
Package 1 Width	10 cm
Package 1 Length	300 cm
Package 1 Weight	2.6 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations