

# Product data sheet

Specifications



Thermistor probe, TeSys LT3,  
integrated triple probe, 160°C, 0 to  
2.5V, bulk qty

DA1TT160

## Main

Range of product	DA1
Product or component type	Thermistor probe
Device short name	DA1TT
Accessory / separate part category	Protection accessory
Quantity per set	Set of 10
Ambient air temperature for operation	160 °C

## Complementary

[Ui] rated insulation voltage	2500 V
[Ue] rated operational voltage	<= 2.5 V
Resistance	250 Ohm per probe 25 °C
Insulation	Reinforced
Cable length	1 m between probe and motor terminal plate 250 mm between probes
Net weight	0.01 kg

## Environment

Standards	IEC 60034-11 Mark A
-----------	---------------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	9.0 cm
Package 1 Length	12.0 cm
Package 1 Weight	9.0 g
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	1.5 cm

Package 2 Width	9.0 cm
Package 2 Length	12.0 cm
Package 2 Weight	95.0 g
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	1.121 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	<a href="#">Yes</a>
California proposition 65	WARNING: Cancer - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)