

Product data sheet

Specifications



Category 6, Patch Cord, UTP, 3M, Grey

DC6PCURJ03GYM

 **Discontinued on:** Dec 15, 2021

 **Discontinued**

Main

Range	Digilink
Product Or Component Type	Patch cord
Cable Shielding Type	UTP
Colour Tint	Grey

Complementary

Type Of Cable	4 twisted-pairs cable
Communication Network Category	6
Connector Type	RJ45
Material	PC (polycarbonate): plug
Awg Gauge	AWG 23 stranded cable
Insulation Resistance	>= 500 mOhm at 500 V DC
Contacts Material	Gold over nickel
[In] Rated Current	1.5 A
Contact Resistance	20 mOhm
[Ue] Rated Operational Voltage	< 72 V DC
Cable Length	3 m

Environment

Standards	ANSI/TIA-568-C.2 Class E ISO/IEC 11801
Product Certifications	ETL verified

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	27 cm
Package 1 Length	33 cm
Package 1 Weight	90 g

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations