

Product data sheet

Specifications



Category 6 UTP 24-port Patch Panel, loaded

DC6PP24UKY1U



Main

Range	Digilink
Product or component type	Patch panel
Provided equipment	With RJ45 connectors
Communication network category	6
Accessory / separate part designation	Insulation displacement connector
Cable shielding type	UTP
Number of port	24

Complementary

Connector type	RJ45
Minimum number of matings	750 cycles
[In] rated current	1.5 A
Insulation resistance	>= 500 mOhm at 500 V DC
Contact resistance	20 mOhm
Material	Panel: steel powder coated
Contacts material	Phosphor bronze with 50 micro-inches gold over 100 micro-inches nickel
Width	482.6 mm
Height	44.2 mm
Number of rack unit	1U

Environment

Environmental characteristic	Flame retardant
Product certifications	UL listed UL/ETL verified
Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 class E EIA/TIA TSB 40 A

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
Package 1 Weight	800.0 g
Package 1 Height	8 cm
Package 1 width	10 cm
Package 1 Length	52 cm
Unit Type of Package 2	P12
Number of Units in Package 2	104
Package 2 Weight	103.38 kg
Package 2 Height	80 cm
Package 2 width	80 cm
Package 2 Length	120 cm
Unit Type of Package 3	S04
Number of Units in Package 3	13
Package 3 Weight	11.422 kg
Package 3 Height	30 cm
Package 3 width	40 cm
Package 3 Length	60 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------