

Product data sheet

Specifications

Category 5e UTP 24-port Patch Panel, loaded



DCEPP24UKY1U

! Discontinued on: 01 March 2023

! To be end-of-service on: 03 April 2023

! To be discontinued

Main

Range	Digilink
Product or component type	Patch panel
Provided equipment	With RJ45 connectors
Communication network category	5e
Cable shielding type	UTP
Number of port	24

Complementary

Connector type	RJ45
Minimum number of matings	750 cycles
[In] rated current	1.5 A
Insulation resistance	≥ 500 mOhm at 500 V DC
Contact resistance	20 mOhm
Material	Panel: steel powder coated
Contacts material	Phosphor bronze with 50 micro-inches gold over 100 micro-inches nickel
Width	482.6 mm
Height	44.2 mm
Number of rack unit	1U

Environment

Environmental characteristic	Flame retardant
Product certifications	UL/ETL verified
Standards	ISO/IEC 11801 class D EIA/TIA TSB 40 A ANSI/TIA-568-C.2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	6 cm
Package 1 Width	8.5 cm
Package 1 Length	49.14 cm
Package 1 Weight	1.05 kg
Unit Type of Package 2	S04
Number of Units in Package 2	13
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	14.09 kg
Unit Type of Package 3	P12
Number of Units in Package 3	104
Package 3 Height	80 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	119.12 kg

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)