


# Product data sheet

Specifications



Auxiliary contact block, TeSys DF,  
1NC, 5A, disconnecter, signalling  
contact, instantaneous

DF22AM1

## Main

Range	TeSys
Device Short Name	DF22
Product Or Component Type	Auxiliary contact block
Auxiliary Contacts Operation	Instantaneous
Pole Contact Composition	1 NC
Connections - Terminals	Faston connector

## Complementary

Range Compatibility	TeSys TeSys DF
[Ui] Rated Insulation Voltage	250 VAC
[Ue] Rated Operational Voltage	24...240 V AC AC-15 24...240 V DC DC-13
[Ith] Conventional Free Air Thermal Current	5 A
Minimum Switching Current	30 mA
Minimum Switching Voltage	10 V
Net Weight	0.032 kg

## Environment

Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-40...80 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	10.5 cm
Package 1 Length	2.0 cm
Package 1 Weight	26.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	100
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.0 cm
Package 2 Weight	3.124 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

<div>✓</div>	Reach Free Of Svhc	
<div>✓</div>	Toxic Heavy Metal Free	
<div>✓</div>	Mercury Free	
<div>✓</div>	Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
California Proposition 65	WARNING: Cancer - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>	