

Product data sheet

Specifications



DIN cartridge fuses, TeSys GS, blade size DIN NH1, fuse type gG, 690VAC, 200A, without striker

DF2HN1201

! To be discontinued on: 31 December 2023

! To be discontinued

Main

Range of product	DF
Range	TeSys
Product or component type	Fuses
Device short name	blade fuse
Device application	Protection
[Ue] rated operational voltage	690 V AC
Fuse size	NH1
Fuse type	DIN

Complementary

[In] rated current	200 A
Fuse curve	GG
Quantity per set	Set of 3
Net weight	0.4 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.3 cm
Package 1 Width	4.5 cm
Package 1 Length	13.8 cm
Package 1 Weight	415.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	18
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.893 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)