


Product data sheet

Specifications

In/Outdoor Non-Armoured Cable, Multi-Mode, 12 Core, 50um, LSZH



DFXAI50GLH12

⚠ Discontinued on: Dec 30, 2016

⚠ End-of-service on: Dec 30, 2019

⚠ Discontinued

Main

Range Of Product	Digilink
Product Or Component Type	Fibre optic cable multi mode
Optic Fibre Type	Non armoured (indoor/outdoor)

Complementary

Optic Fiber Core	50 µm
Condition Of Use	Indoor/outdoor
Cable Weight	90 kg / 1 km
Bending Radius	20 x overall diameter
Number Of Optic Fibre	12
Tensile Strength	2670 N
Crush Resistance	0.044 N/m

Environment

Ambient Air Temperature For Operation	-30...70 °C
Ambient Air Temperature For Storage	-40...75 °C
Standards	TIA/EIA-568-B ISO/IEC 11801

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications