

# Product data sheet

Specifications

## ST Adaptor, Simplex, Multi-Mode, Phosphor Bronze Sleeve



DFXDSTTYPXPM

 **Discontinued on:** Feb 14, 2019

 **Discontinued**

### Main

Product Or Component Type      Multi-mode adaptor

### Complementary

Connector Type	ST
Exchange Mode	Simplex
Maximum Insertion Loss	0.3 dB
Minimum Number Of Matings	1000 cycles
Product Compatibility	For 50/125 and 62.5/125 µm optical fibre
Contacts Material	Phosphor bronze

### Environment

Ambient Air Temperature For Operation	-40...80 °C
Product Certifications	UL listed
Standards	ISO/IEC 11081 EIA/TIA-568-C.0 IEC 874

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	9 cm
Package 1 Length	15 cm
Package 1 Weight	40 g

### Contractual warranty

Warranty      18 months

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications