


# Product data sheet

Specifications



## Category 3 100 pair UTP Cable 305m

DXYCAT3UT100P

⚠ Discontinued on: Dec 31, 2018

⚠ Discontinued

### Main

Product Or Component Type	Copper cable
Cable Shielding Type	UTP
Communication Network Category	3
Colour Tint	Grey

### Complementary

Type Of Cable	100 pairs cable
Nominal Velocity Propagation	69 %
Capacitance Unbalance	3.28 pF / 1 m
Cable Outer Diameter	22 mm
Cable Length	305 m
Awg Gauge	AWG 24
Thickness	Insulation: 0.2 mm Jacket: 1.3 mm
Pulling Force	40 N
Material	PVC (polyvinyl chloride): jacket

### Environment

Standards	ISO/IEC 11801 ANSI/TIA-568-A
-----------	---------------------------------

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Eu Rohs Directive		Under investigation
China Rohs Regulation		<a href="#">China RoHS declaration</a>
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins