

# Product data sheet

Specifications



## 13A 3 Pin Switched Socket Outlet, Grey Silver

E3015\_GS

### Main

|                            |                             |
|----------------------------|-----------------------------|
| Range                      | Neo C-Metro                 |
| Product or component type  | Power socket-outlet         |
| Switch function            | 1-pole                      |
| Outlet poles configuration | 3P with shutters            |
| Outlet standard            | MS 589<br>SS 145<br>BS 1363 |
| Colour tint                | Grey silver                 |

### Complementary

|                         |   |
|-------------------------|---|
| Wiring device mounting  | Flush<br>Surface  |
| Rated current           | 13 A at 250 V AC 50/60 Hz   |
| Material                | Brass: contact<br>Copper with silver onlay: bridge<br>Nylon: shutter<br>Polycarbonate: grid plate<br>Polycarbonate: surround<br>Steel with brass plating: screws<br>Steel with brass plating: terminals |
| Load type               | Resistive   |
| Connections - terminals | Pillar terminals  |
| Width                   | 87 mm   |
| Height                  | 87 mm   |
| Depth                   | 17 mm   |

### Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Ambient air temperature for operation | 0...40 °C                   |
| Relative humidity                     | 0...95 %                    |
| Environmental characteristic          | Indoor use                  |
| Standards                             | SS 145<br>BS 1363<br>MS 589 |

## Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Weight             | 81.0 g     |
| Package 1 Height             | 1.7 cm     |
| Package 1 Width              | 8.7 cm     |
| Package 1 Length             | 8.7 cm     |
| Unit Type of Package 2       | PAL        |
| Number of Units in Package 2 | 3200       |
| Package 2 Weight             | 312800.0 g |
| Package 2 Height             | 1400.0 mm  |
| Package 2 Width              | 1140.0 mm  |
| Package 2 Length             | 1140.0 mm  |
| Unit Type of Package 3       | BB1        |
| Number of Units in Package 3 | 8          |
| Package 3 Weight             | 662.0 g    |
| Package 3 Height             | 15.0 cm    |
| Package 3 Width              | 19.0 cm    |
| Package 3 Length             | 8.0 cm     |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Recommended replacement(s)