

Product data sheet

Specifications



10A Fused Connection Unit with Double Pole Switch and White LED, White

E3031DFSG10_EWWW

⚠ Discontinued on: Dec 9, 2016

⚠ Discontinued

Main

Range	Neo
Product Or Component Type	Fused connection unit
Switch Function	1-pole
Bulb Type	LED, red
Colour Tint	White
Standards	BS 5733

Complementary

Wiring Device Mounting	Surface Flush
Rated Current	10 A at 250 V AC 50 Hz
Contacts Material	Brass Phosphor bronze
Load Type	Resistive
Protection Type	Fuse
Material	Polycarbonate: grid plate Polycarbonate: surround
Number Of Cables	2 x 4 mm ² input 1 x 1.5 mm ² output 1 x 2.5 mm ² output 3 x 0.5...1.5 mm ² output 3 x 2.5 mm ² input
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

