

Product data sheet

Specifications



Electronic Key Card Switch with Indicator, Grey Silver

E3031EKTH_GS

Main

Range of product	Neo C-Metro
Product or component type	Key card switch
Bulb type	LED, blue
Rated current	16 A at 250 V AC 50/60 Hz
Colour tint	Grey silver

Complementary

Wiring device mounting	Flush Surface
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Load type	Resistive
Clamping connection capacity	1 x 4 mm ² for stranded cable(s) 2 x 4 mm ² for stranded cable(s) 1 x 2.5 mm ² for solid cable(s) 1 x 2.5 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s) 2 x 2.5 mm ² for stranded cable(s) 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	25 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	IEC 60669-2-1 GB 16915.2

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
Package 1 Height	21 cm
Package 1 Width	32.5 cm
Package 1 Length	50 cm
Package 1 Weight	162.434 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	6 cm
Package 2 Weight	975 g
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	9746.04 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)