

# Product data sheet

Specifications



## Electronic Key Card Switch with Indicator, White

E3031EKTH\_WW

! Discontinued on: 30 September 2022

! Discontinued

### Main

Range of product	Neo C-Metro
Product or component type	Key card switch
Bulb type	LED, blue
Rated current	16 A at 250 V AC 50/60 Hz
Colour tint	White

### Complementary

Wiring device mounting	Surface Flush
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Load type	Resistive
Clamping connection capacity	1 x 4 mm <sup>2</sup> for stranded cable(s) 2 x 4 mm <sup>2</sup> for stranded cable(s) 1 x 2.5 mm <sup>2</sup> for solid cable(s) 1 x 2.5 mm <sup>2</sup> for stranded cable(s) 2 x 2.5 mm <sup>2</sup> for solid cable(s) 2 x 2.5 mm <sup>2</sup> for stranded cable(s) 3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	25 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	GB 16915.2 IEC 60669-2-1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21 cm
Package 1 Width	32.5 cm
Package 1 Length	50 cm
Package 1 Weight	162.434 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	974.604 g
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	9746.04 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)