

Product data sheet

Specifications



1 Gang 1 Way Horizontal Dolly Switch with Blue LED, Grey Silver

E3031H1_EBGS

Main

| | |
|---------------------------|-----------------------------------------------------------------|
| Range | Neo |
| Product or component type | Control switch |
| Device application | Control |
| Wiring device mounting | Flush Surface |
| Switch function | 1-way |
| Switch application | Switch |
| Load type | Fluorescent lamp Resistive Incandescent lamp Inductive |
| Bulb type | LED (blue) |
| Colour tint | Grey silver |

Complementary

| | |
|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rated current | 10 A at 250 V AC 50/60 Hz |
| Number of gangs | 1 gang horizontal |
| Material | Brass: metal parts Polycarbonate: plastic part Steel: metal parts |
| Clamping connection capacity | 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s) |
| Connections - terminals | Pillar terminals |
| Width | 87 mm |
| Height | 87 mm |
| Embedding depth | 23.5 mm |
| Depth | 36 mm |

Environment

| | |
|---------------------------------------|------------|
| Ambient air temperature for operation | 0...40 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | Indoor use |

| | |
|------------------|-----------------------------------------|
| Standards | GB 16915.1 EN 60669-1 IEC 60669-1 |
|------------------|-----------------------------------------|

Packing Units

| | |
|-------------------------------|-----|
| Unit Type of Package 1 | PCE |
|-------------------------------|-----|

| | |
|-------------------------------------|---|
| Number of Units in Package 1 | 1 |
|-------------------------------------|---|

| | |
|-------------------------|--------|
| Package 1 Height | 3.6 cm |
|-------------------------|--------|

| | |
|------------------------|--------|
| Package 1 Width | 8.7 cm |
|------------------------|--------|

| | |
|-------------------------|--------|
| Package 1 Length | 8.7 cm |
|-------------------------|--------|

| | |
|-------------------------|------|
| Package 1 Weight | 68 g |
|-------------------------|------|

| | |
|-------------------------------|-----|
| Unit Type of Package 2 | BB1 |
|-------------------------------|-----|

| | |
|-------------------------------------|---|
| Number of Units in Package 2 | 8 |
|-------------------------------------|---|

| | |
|-------------------------|-------|
| Package 2 Height | 15 cm |
|-------------------------|-------|

| | |
|------------------------|-------|
| Package 2 Width | 19 cm |
|------------------------|-------|

| | |
|-------------------------|------|
| Package 2 Length | 8 cm |
|-------------------------|------|

| | |
|-------------------------|-------|
| Package 2 Weight | 558 g |
|-------------------------|-------|

| | |
|-------------------------------|-----|
| Unit Type of Package 3 | CAR |
|-------------------------------|-----|

| | |
|-------------------------------------|----|
| Number of Units in Package 3 | 80 |
|-------------------------------------|----|

| | |
|-------------------------|-------|
| Package 3 Height | 21 cm |
|-------------------------|-------|

| | |
|------------------------|-------|
| Package 3 Width | 31 cm |
|------------------------|-------|

| | |
|-------------------------|-------|
| Package 3 Length | 50 cm |
|-------------------------|-------|

| | |
|-------------------------|--------|
| Package 3 Weight | 6580 g |
|-------------------------|--------|

Offer Sustainability

| | |
|--------------------------|---------------------|
| EU RoHS Directive | Under investigation |
|--------------------------|---------------------|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty | 18 months |
|-----------------|-----------|

Recommended replacement(s)