

# Product data sheet

Specifications



## 600W 1 Gang Horizontal Dimming Switch with Blue LED, Grey Silver

E3031HD\_EBGS

### Main

Range	Neo C-Metro
Product or component type	Dimmer
Bulb type	LED, blue
Number of gangs	1 gang
Colour tint	Grey silver

### Complementary

Wiring device mounting	Surface Flush
Power range	40...600 VA incandescent lamp 40...600 VA low voltage halogen lamp with electronic transformer
[Ue] rated operational voltage	220...240 V AC 50/60 Hz
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping connection capacity	1 x 4 mm <sup>2</sup> for stranded cable(s) 2 x 4 mm <sup>2</sup> for stranded cable(s) 1 x 2.5 mm <sup>2</sup> for solid cable(s) 1 x 2.5 mm <sup>2</sup> for stranded cable(s) 2 x 2.5 mm <sup>2</sup> for solid cable(s) 2 x 2.5 mm <sup>2</sup> for stranded cable(s) 3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	26 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	GB 16915.2 IEC 60669-2-1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	32.5 cm
Package 1 Length	50.0 cm
Package 1 Weight	135.225 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)