

Product data sheet

Specifications



600W 1 Gang Horizontal Dimming Switch with White LED, White

E3031HD_EWWW

Main

Range	Neo C-Metro
Product or component type	Dimmer
Bulb type	LED, white
Number of gangs	1 gang
Colour tint	White

Complementary

Wiring device mounting	Flush Surface
Power range	40...600 VA incandescent lamp 40...600 VA low voltage halogen lamp with electronic transformer
[Ue] rated operational voltage	220...240 V AC 50/60 Hz
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping connection capacity	1 x 4 mm ² for stranded cable(s) 2 x 4 mm ² for stranded cable(s) 1 x 2.5 mm ² for solid cable(s) 1 x 2.5 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s) 2 x 2.5 mm ² for stranded cable(s) 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	26 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	GB 16915.2 IEC 60669-2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	32.5 cm
Package 1 Length	50.0 cm
Package 1 Weight	135.225 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)