

Product data sheet

Specifications



1 Gang RJ11 4 Pin Telephone Outlet, Grey Silver

E3031RJ_GS

Main

Product Or Component Type	Telephone socket
Telephone Socket Type	RJ11 (4 contacts) - category 3
Colour Tint	Grey silver

Complementary

Wiring Device Mounting	Flush Surface
Socket Number	1
Rated Current	1.5 A at 125 Vrms AC
Number Of Gangs	1 gang
Material	PBT 15 % FG: insert PC: housing Polycarbonate: plastic part
Contacts Material	Contact: phosphor bronze IDC contact: phosphor bronze with tin plating
Contact Resistance	1000000 µOhm
Insulation Resistance	>= 1000 MOhm
Awg Gauge	AWG 26...AWG 24 (2 twisted pair cables)
Width	87 mm
Height	87 mm
Depth	36 mm

Environment

Dielectric Strength	750 V for 60 s at 60 Hz
Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	BS 5733 GB 17466

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	68 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	558 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6580 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations