

Product data sheet

Specifications



1 Gang RJ11 4 Pin Telephone Outlet, White

E3031RJ_WW

Main

Product or component type	Telephone socket
Telephone socket type	RJ11 (4 contacts) - category 3
Colour tint	White

Complementary

Wiring device mounting	Flush Surface
Socket number	1
Rated current	1.5 A at 125 Vrms AC
Number of gangs	1 gang
Material	PBT 15 % FG: insert PC: housing Polycarbonate: plastic part
Contacts material	Contact: phosphor bronze IDC contact: phosphor bronze with tin plating
Contact resistance	1000000 μ Ohm
Insulation resistance	\geq 1000 MOhm
AWG gauge	AWG 26...AWG 24 (2 twisted pair cables)
Width	87 mm
Height	87 mm
Depth	36 mm

Environment

Dielectric strength	750 V for 60 s at 60 Hz
Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	BS 5733 GB 17466

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
Package 1 Weight	68.0 g
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	3200
Package 2 Weight	271200.0 g
Package 2 Height	140 cm
Package 2 Width	114 cm
Package 2 Length	114 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	558.0 g
Package 3 Height	9.5 cm
Package 3 Width	15 cm
Package 3 Length	19 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
-----------------	-----------

Recommended replacement(s)