

# Product data sheet

Specifications



## 1 Gang TV Socket Outlet, White

E3031TV\_WW

### Main

Range of product	Neo C-Metro
Product or component type	TV socket
Socket number	1
Colour tint	White

### Complementary

Wiring device mounting	Flush Surface
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Bandwidth	5...862 MHz TV
Maximum insertion loss	1 dB
Connections - terminals	Pillar terminal without pressure plate Saddle terminal
Width	87 mm
Height	87 mm
Depth	27.5 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	BS 3041

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	68.0 g
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm

Package 1 Length	8.7 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	3200
Package 2 Weight	271200.0 g
Package 2 Height	140 cm
Package 2 Width	114 cm
Package 2 Length	114 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	558.0 g
Package 3 Height	15 cm
Package 3 Width	19 cm
Package 3 Length	8 cm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)