

Product data sheet

Specifications



2 Gang 1 Way Horizontal Dolly Switch with Blue LED, Grey Silver

E3032H1_EBGS

Main

Range	Neo
Product or component type	Control switch
Wiring device mounting	Flush Surface
Switch function	1-way
Switch application	Switch
Load type	Fluorescent lamp Incandescent lamp Inductive Resistive
Bulb type	LED (blue)
Colour tint	Grey silver

Complementary

Rated current	10 A at 250 V AC 50/60 Hz
Number of gangs	2 gangs horizontal
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	23.5 mm
Depth	36 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	GB 16915.1 EN 60669-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	92.0 g
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	3200
Package 2 Weight	348000.0 g
Package 2 Height	140 cm
Package 2 Width	114 cm
Package 2 Length	114 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	750.0 g
Package 3 Height	15 cm
Package 3 Width	19 cm
Package 3 Length	8 cm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)