

Product data sheet

Specifications



3 Gang 2 Way Horizontal Dolly Switch with Blue LED, Grey Silver

E3033H2_EBGS

Main

| | |
|---------------------------|---|
| Range | Neo |
| Product or component type | Control switch |
| Device application | Control |
| Wiring device mounting | Surface Flush |
| Switch function | 2-way |
| Switch application | Switch |
| Load type | Inductive Incandescent lamp Resistive Fluorescent lamp |
| Bulb type | LED (blue) |
| Colour tint | Grey silver |

Complementary

| | |
|------------------------------|--|
| Rated current | 10 A at 250 V AC 50/60 Hz |
| Number of gangs | 3 gangs horizontal |
| Material | Brass: metal parts Polycarbonate: plastic part Steel: metal parts |
| Clamping connection capacity | 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s) |
| Connections - terminals | Pillar terminals |
| Width | 87 mm |
| Height | 87 mm |
| Embedding depth | 23.5 mm |
| Depth | 36 mm |

Environment

| | |
|---------------------------------------|------------|
| Ambient air temperature for operation | 0...40 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | Indoor use |

| | |
|-----------|---|
| Standards | IEC 60669-1 EN 60669-1 GB 16915.1 |
|-----------|---|

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.6 cm |
| Package 1 Width | 8.7 cm |
| Package 1 Length | 8.7 cm |
| Package 1 Weight | 100 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 8 |
| Package 2 Height | 15 cm |
| Package 2 Width | 19 cm |
| Package 2 Length | 8 cm |
| Package 2 Weight | 814 g |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 80 |
| Package 3 Height | 21 cm |
| Package 3 Width | 31 cm |
| Package 3 Length | 50 cm |
| Package 3 Weight | 9140 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)