

Product data sheet

Specifications



4 Gang 1 Way Horizontal Dolly Switch with White LED, White

E3034H1_EWWW

Main

| | |
|---------------------------|---|
| Range | Neo |
| Product Or Component Type | Control switch |
| Wiring Device Mounting | Surface Flush |
| Switch Function | 1-way |
| Switch Application | Switch |
| Load Type | Inductive Incandescent lamp Fluorescent lamp Resistive |
| Bulb Type | LED (white) |
| Colour Tint | White |

Complementary

| | |
|------------------------------|--|
| Rated Current | 10 A at 250 V AC 50/60 Hz |
| Number Of Gangs | 4 gangs horizontal |
| Material | Brass: metal parts Polycarbonate: plastic part Steel: metal parts |
| Clamping Connection Capacity | 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s) |
| Connections - Terminals | Pillar terminals |
| Width | 87 mm |
| Height | 87 mm |
| Embedding Depth | 23.5 mm |
| Depth | 36 mm |

Environment

| | |
|---------------------------------------|---|
| Ambient Air Temperature For Operation | 0...40 °C |
| Relative Humidity | 0...95 % |
| Environmental Characteristic | Indoor use |
| Standards | IEC 60669-1 EN 60669-1 GB 16915.1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.6 cm |
| Package 1 Width | 8.7 cm |
| Package 1 Length | 8.7 cm |
| Package 1 Weight | 102 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 8 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 15 cm |
| Package 2 Length | 19 cm |
| Package 2 Weight | 830 g |
| Unit Type Of Package 3 | CAR |
| Number Of Units In Package 3 | 80 |
| Package 3 Height | 21 cm |
| Package 3 Width | 31 cm |
| Package 3 Length | 50 cm |
| Package 3 Weight | 9300 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | | |
|-----------------------|----------------------------|---|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | | REACH Declaration |
| | | |
| Eu Rohs Directive | | Compliant EU RoHS Declaration |
| | | |
| China Rohs Regulation | | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |