

# Product data sheet

Specifications



## 13A 250V 1 Gang Switched Socket with Neon, White

E8215N\_WE

### Main

Product or component type	Power socket-outlet
Switch function	Switch
Rated current	13 A at 250 V AC 50...60 Hz
Number of gangs	1 gang
Load type	Resistive
Cover frame colour tint	White

### Complementary

Wiring device mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping connection capacity	2 x 4 mm <sup>2</sup> for stranded cable(s) 3 x 2.5 mm <sup>2</sup> for solid cable(s)
Width	87 mm
Height	87 mm
Depth	26.6 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	BS 1363-2 MS 589-2 SS 145-2

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.72 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	103 g

<b>Unit Type of Package 2</b>	BB1
<b>Number of Units in Package 2</b>	8
<b>Package 2 Height</b>	9.5 cm
<b>Package 2 Width</b>	15 cm
<b>Package 2 Length</b>	19 cm
<b>Package 2 Weight</b>	824 g
<b>Unit Type of Package 3</b>	CAR
<b>Number of Units in Package 3</b>	80
<b>Package 3 Height</b>	32.5 cm
<b>Package 3 Width</b>	32.5 cm
<b>Package 3 Length</b>	50 cm
<b>Package 3 Weight</b>	8702.64 g

### **Contractual warranty**

<b>Warranty</b>	18 months
-----------------	-----------

### **Recommended replacement(s)**