

Product data sheet

Specifications



13A 250V 1 Gang Switched Socket, White

E8215_WE

Main

Product or component type	Power socket-outlet
Switch function	Switch
Rated current	13 A at 250 V AC 50...60 Hz
Number of gangs	1 gang
Load type	Resistive
Cover frame colour tint	White

Complementary

Wiring device mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping connection capacity	2 x 4 mm ² for stranded cable(s) 3 x 2.5 mm ² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	26.6 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	BS 1363-2 SS 145-2 MS 589-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	108.0 g
Package 1 Height	2.7 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm

Unit Type of Package 2	PAL
Number of Units in Package 2	1600
Package 2 Weight	181800.0 g
Package 2 Height	86 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	824.0 g
Package 3 Height	9.5 cm
Package 3 Width	15 cm
Package 3 Length	19 cm

Contractual warranty

Warranty	18 months
-----------------	-----------

Recommended replacement(s)